


DVD-2BC4A-24D Cut Sheet



NITRA solenoid valve, 2-way, 2-position, N.C., glass-filled nylon body, 1/2in female NPT inlet(s), 1/2in female NPT outlet(s), Cv=2.45, 24 VDC operating voltage, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DVD-2BC4A-24D>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air, oil, inert gas or water
Valve Type	Solenoid process
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return
Body Material	Glass-filled nylon
Inlet Port	1/2in female NPT
Outlet Port	1/2in female NPT
Flow Coefficient	2.45
Operating Voltage	24 VDC
Electrical Connection	11mm DIN style wiring plug
Form Factor	Standard
Includes	Viton seals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	None