

DVD-2BC6F-24D Cut Sheet



NITRA solenoid valve, 2-way, 2-position, N.C., brass and composite body, 1in female NPT inlet(s), 1in female NPT outlet(s), Cv=14, 24 VDC operating voltage, 18mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DVD-2BC6F-24D>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air, oil, inert gas or water
Valve Type	Solenoid process
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return
Body Material	Brass and composite
Inlet Port	1in female NPT
Outlet Port	1in female NPT
Flow Coefficient	14
Operating Voltage	24 VDC
Electrical Connection	18mm DIN style wiring plug
Form Factor	Standard
Includes	Viton seals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document