

DVM-2BC1B-24D Cut Sheet



NITRA solenoid valve, 2-way, 2-position, N.C., glass-filled nylon body, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), Cv=0.065, 24 VDC operating voltage, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DVM-2BC1B-24D>

Technical Specifications

| | |
|------------------------------|----------------------------------|
| Brand | NITRA |
| Item | Valve |
| Working Fluid | Air, gases, water or chemicals |
| Valve Type | Solenoid media separated process |
| Port Quantity | 2-way |
| Number Of Positions | 2 |
| Valve Configuration | N.C. |
| Action | Single solenoid spring return |
| Body Material | Glass-filled nylon |
| Inlet Port | 1/8in female NPT |
| Outlet Port | 1/8in female NPT |
| Flow Coefficient | 0.065 |
| Operating Voltage | 24 VDC |
| Electrical Connection | 11mm DIN style wiring plug |
| Form Factor | Standard |
| Includes | Viton seals |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |