

DVM-2BC3G-24D Cut Sheet



NITRA solenoid valve, 2-way, 2-position, N.C., glass-filled nylon body, 3/8in female NPT inlet(s), 3/8in female NPT outlet(s), Cv=0.52, 24 VDC operating voltage, 18mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DVM-2BC3G-24D>

Technical Specifications

| | |
|----------------------------|---|
| Brand | NITRA |
| Item | Valve |
| Working Fluid | Pneumatic, oil, inert gas or medical fluids |
| Valve Type | Solenoid media separated process |
| Port Quantity | 2-way |
| Number Of Positions | 2 |
| Valve Configuration | N.C. |
| Action | Single solenoid spring return |

| | |
|------------------------------|----------------------------|
| Body Material | Glass-filled nylon |
| Inlet Port | 3/8in female NPT |
| Outlet Port | 3/8in female NPT |
| Flow Coefficient | 0.52 |
| Operating Voltage | 24 VDC |
| Electrical Connection | 18mm DIN style wiring plug |
| Includes | Viton seals |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DVM-2BC3G-24D.pdf>
See store item page for other formats.