

DVP-2CC1C-24A Cut Sheet



NITRA solenoid valve, 2-way, 2-position, N.C., glass-filled nylon body, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), stackable, Cv=0.08, 24 VAC operating voltage, 11mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DVP-2CC1C-24A>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Pneumatic, oil, inert gas, water or caustics
Valve Type	Solenoid process
Port Quantity	2-way
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return

Body Material	Glass-filled nylon
Inlet Port	1/8in female NPT
Outlet Port	1/8in female NPT
Stackable	Yes
Flow Coefficient	0.08
Operating Voltage	24 VAC
Electrical Connection	11mm DIN style wiring plug
Includes	Viton seals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DVP-2CC1C-24A.pdf>
See store item page for other formats.