

DVP-3DC2E-24A Cut Sheet



NITRA solenoid valve, 3-way, 2-position, N.C., glass-filled nylon body, 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=0.245, 24 VAC operating voltage, 18mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DVP-3DC2E-24A>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air, oil, inert gas, water or caustics
Valve Type	Solenoid process
Port Quantity	3-way
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return
Body Material	Glass-filled nylon
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Flow Coefficient	0.245
Operating Voltage	24 VAC
Electrical Connection	18mm DIN style wiring plug
Form Factor	Standard
Includes	Viton seals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document