

E22KB62A Cut Sheet



Eaton selector switch, 22mm, 2-position, spring return from right, key removable in all positions, (1) N.O. contact(s), plastic base, plastic bezel, Operator: black, key, 30mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/E22KB62A>

Technical Specifications

Brand	Eaton
Item	Selector switch
Barrel Size	22mm
NEMA Rating	1/2/3/3R/4/4X/12/13
IP Rating	IP65 and IP66
Number Of Positions	2
Action	Spring return from right
Key Removable Position	Key removable in all positions

Contact Type	(1) N.O.
Base Material	Plastic
Bezel Material	Plastic
Operator Color	Black
Operator Type	Key
Operator Size	30mm
Operator Shape	Round
Operator Material	Plastic

Agency Approvals

UL Listed File #	E131568
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	68551
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/E22KB62A.pdf>
See store item page for other formats.