

EA1-T6CL Cut Sheet



C-more Micro EA1 series touch screen HMI, 6in color TFT LCD, 320 x 240 pixel, QVGA, LED backlight, supports (1) serial and (1) USB port.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EA1-T6CL>

Technical Specifications

Brand	C-more Micro
Item	HMI
Series	EA1
Touch Screen	Yes
Display Size	6in
Viewable Size	5.7in
Display Type	Color TFT LCD
Widescreen	No
Display Maximum Colors	32K colors
Display Resolution (W x H)	320 x 240 pixel
Display Video Standard	QVGA

Display Orientation	Landscape/portrait
Backlight Type	LED
Power Requirement	24 VDC
Housing Rating	NEMA 4/4X
Environmental Requirements	Indoor use only
IP Rating	IP65
Serial Ports	(1) RS-232/422/485
USB Ports	(1) 2.0 Type B
Software Required	EA-MG-PGMSW programming software v2.5 or later
Includes	Mounting hardware, gasket and cutout template

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	234884
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/EA1-T6CL.pdf>
See store item page for other formats.