

# EA3-S3ML-RN Cut Sheet



C-more Micro EA3 series HMI, 3in monochrome STN LCD, 128 x 64 pixel, LED backlight, (1) serial port.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EA3-S3ML-RN>

## Technical Specifications

<b>Brand</b>	C-more Micro
<b>Item</b>	HMI
<b>Series</b>	EA3
<b>Touch Screen</b>	No
<b>Display Size</b>	3in
<b>Viewable Size</b>	3.1in
<b>Display Type</b>	Monochrome STN LCD
<b>Widescreen</b>	No
<b>Display Maximum Colors</b>	Monochrome
<b>Display Resolution</b>	128 x 64 pixel
<b>Brightness</b>	150nits
<b>Display Orientation</b>	Landscape
<b>Backlight Type</b>	LED
<b>External Power Requirement</b>	5 VDC
<b>Housing Rating</b>	NEMA 1 (NEMA 4/4X when installed with optional EA-MG-S3ML-GSK Gasket)
<b>Environmental Requirements</b>	Indoor use only

<b>IP Rating</b>	IP20 (IP65 when installed with optional EA-MG-S3ML-GSK Gasket)
<b>Mounting</b>	Panel
<b>Communication Port and Connection Type(s)</b>	(1) RS-232 (RJ12)
<b>Port Protocol(s)</b>	<ul style="list-style-type: none"><li>AutomationDirect Productivity Series</li><li>AutomationDirect Do-more/BRX</li><li>AutomationDirect CLICK</li><li>AutomationDirect DirectLOGIC K-Sequence</li><li>AutomationDirect DirectLOGIC DirectNET</li><li>AutomationDirect Modbus RTU Master</li><li>Modicon Modbus RTU Master</li><li>Entivity Modbus RTU Master</li></ul>
<b>Port Speed(s)</b>	up to 38.4k baud
<b>Programming Software</b>	EA-MG-PGMSW programming software v4.3 or later
<b>Includes</b>	Mounting hardware
<b>Additional Information</b>	Power is supplied to the panel through the RJ12 port when used with AutomationDirect PLC's

## Agency Approvals

<b>UL Listed File #</b>	E157382
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/EA3-S3ML-RN.pdf>  
See store item page for other formats.