

EA3-S3ML-R Cut Sheet



C-more Micro EA3 series touch screen HMI, 3in monochrome STN LCD, analog resistive, 128 x 64 pixel, LED backlight, (1) serial port.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EA3-S3ML-R>

Technical Specifications

Brand	C-more Micro	Environmental Requirements	Indoor use only
Item	HMI	IP Rating	IP65
Series	EA3	Mounting	Panel
Touch Screen	Yes	Communication Port and Connection Type(s)	(1) RS-232 (RJ12)
Display Size	3in	Port Protocol(s)	<ul style="list-style-type: none">AutomationDirect Productivity SeriesAutomationDirect Do-more/BRXAutomationDirect CLICKAutomationDirect DirectLOGIC K-SequenceAutomationDirect DirectLOGIC DirectNETAutomationDirect Modbus RTU MasterModicon Modbus RTU MasterEntivity Modbus RTU Master
Viewable Size	3.1in	Port Speed(s)	up to 38.4k baud
Display Type	Monochrome STN LCD	Programming Software	EA-MG-PGMSW programming software v4.3 or later
Widescreen	No	Includes	Mounting hardware and gasket
Display Maximum Colors	Monochrome	Additional Information	Power is supplied to the panel through the RJ12 port when used with AutomationDirect PLC's
Display Resolution	128 x 64 pixel		
Touch Panel Type	Analog resistive		
Brightness	150nits		
Display Orientation	Landscape		
Backlight Type	LED		
External Power Requirement	5 VDC		
Housing Rating	NEMA 4/4X		

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/EA3-S3ML-R.pdf>
See store item page for other formats.