

# EC-M12F12-LKT12-05 Cut Sheet



Lika Electronic encoder cable, M12 axial female to pigtail, shielded, 16.4ft/5m cable length. For use with Lika Electronic AQ58 and AQ59 series encoders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EC-M12F12-LKT12-05>

## Technical Specifications

<b>Brand</b>	Lika Electronic
<b>Item</b>	Cable
<b>Cable Type</b>	Encoder
<b>Replacement</b>	No
<b>Connection 1</b>	M12 axial female
<b>Connection 2</b>	Pigtail
<b>Shielded</b>	Yes
<b>Twisted Pair</b>	No
<b>Cable Length</b>	16.4ft/5m
<b>Conductor Size</b>	24 AWG
<b>For Use With</b>	Lika Electronic AQ58 and AQ59 series encoders

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/EC-M12F12-LKT12-05.pdf>  
See store item page for other formats.