

EC-M12FC-LKCB-05 Cut Sheet



Lika Electronic encoder cable, M12 axial female to pigtail, shielded, twisted pair, 16.4ft/5m cable length. For use with Lika Electronic Modbus RTU encoders.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EC-M12FC-LKCB-05>

Technical Specifications

Brand	Lika Electronic
Item	Cable
Cable Type	Encoder
Replacement	No
Connection 1	M12 axial female
Connection 2	Pigtail
Shielded	Yes
Twisted Pair	Yes
Cable Length	16.4ft/5m
Conductor Size	24 AWG and 22 AWG
For Use With	Lika Electronic Modbus RTU encoders

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/EC-M12FC-LKCB-05.pdf>
See store item page for other formats.