


ECP3107 Cut Sheet



NITRA pneumatic pushbutton, IP65, 22mm, momentary, operator only, plastic base, plastic bezel, black, Operator: green, flush, 30mm, round, plastic, operator text "(I)".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECP3107>

Technical Specifications

Brand	NITRA
Item	Pushbutton
Working Fluid	Air or inert gas
IP Rating	IP65
Barrel Size	22mm
Action	Momentary
Contact Type	Operator only
Base Material	Plastic
Bezel Material	Plastic

Bezel Color	Black
Operator Color	Green
Operator Type	Flush
Operator Size	30mm
Operator Shape	Round
Operator Material	Plastic
Operator Legend	(I)
Text Color	White

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ECP3107.pdf>
See store item page for other formats.