

ECP3107 Cut Sheet



NITRA pneumatic pushbutton, IP65, 22mm, momentary, operator only, plastic base, plastic bezel, black, Operator: green, flush, 30mm, round, plastic, operator text "(I)".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECP3107>

Technical Specifications

| | |
|--------------------------|----------------------|
| Brand | NITRA |
| Item | Pneumatic pushbutton |
| IP Rating | IP65 |
| Barrel Size | 22mm |
| Action | Momentary |
| Contact Type | Operator only |
| Base Material | Plastic |
| Bezel Material | Plastic |
| Bezel Color | Black |
| Operator Color | Green |
| Operator Type | Flush |
| Operator Size | 30mm |
| Operator Shape | Round |
| Operator Material | Plastic |
| Operator Legend | (I) |
| Text Color | White |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |