

ECP3310 Cut Sheet



NITRA pneumatic selector switch, IP65, 22mm, 2-position, spring return from right, operator only, plastic base, plastic bezel, Operator: black, knob, 30mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECP3310>

Technical Specifications

Brand	NITRA
Item	Pneumatic selector switch
Working Fluid	Pneumatic
Barrel Size	22mm
IP Rating	IP65
Number Of Positions	2
Action	Spring return from right
Contact Type	Operator only

Base Material	Plastic
Bezel Material	Plastic
Operator Color	Black
Operator Type	Knob
Operator Size	30mm
Operator Shape	Round
Operator Material	Plastic

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ECP3310.pdf>
See store item page for other formats.