

# ECP3380 Cut Sheet



NITRA pneumatic selector switch, IP65, 22mm, 3-position, spring return to center from right or left, operator only, plastic base, plastic bezel, Operator: black, lever, 30mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECP3380>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Pneumatic selector switch
<b>Barrel Size</b>	22mm
<b>IP Rating</b>	IP65
<b>Number Of Positions</b>	3
<b>Action</b>	Spring return to center from right or left
<b>Contact Type</b>	Operator only
<b>Base Material</b>	Plastic
<b>Bezel Material</b>	Plastic
<b>Operator Color</b>	Black
<b>Operator Type</b>	Lever
<b>Operator Size</b>	30mm
<b>Operator Shape</b>	Round
<b>Operator Material</b>	Plastic

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>