

# ECP3430 Cut Sheet



NITRA pneumatic selector switch, IP65, 22mm, 2-position, spring return from right, key removable left position, operator only, plastic base, plastic bezel, Operator: black, key, 30mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECP3430>

## Technical Specifications

Brand	NITRA
Item	Pneumatic selector switch
Working Fluid	Pneumatic
Barrel Size	22mm
IP Rating	IP65
Number Of Positions	2
Action	Spring return from right
Key Removable Position	Key removable left position

Contact Type	Operator only
Base Material	Plastic
Bezel Material	Plastic
Operator Color	Black
Operator Type	Key
Operator Size	30mm
Operator Shape	Round
Operator Material	Plastic

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/ECP3430.pdf>  
See store item page for other formats.