

ECX1512 Cut Sheet



AutomationDirect selector switch, IP65, 22mm, 2-position, maintained, (2) N.O. contact(s), metal base, metal bezel, Operator: black, joystick, 30mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECX1512>

Technical Specifications

Brand	AutomationDirect
Item	Selector switch
Barrel Size	22mm
IP Rating	IP65
Number Of Positions	2
Action	Maintained
Contact Type	(2) N.O.
Base Material	Metal
Bezel Material	Metal
Operator Color	Black
Operator Type	Joystick
Operator Size	30mm
Operator Shape	Round
Operator Material	Plastic
Connection	Screw terminals

Agency Approvals

UL Listed File #	None
UL Recognized File #	E189258
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ECX1512.pdf>
See store item page for other formats.