

ECX2070-127 Cut Sheet



AutomationDirect audible alarm buzzer, 80 dB at 10cm, 2.4 kHz tone frequency, pulse tone(s), 120 VAC/VDC, 22mm, panel mount, plastic housing, black, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECX2070-127>

Technical Specifications

Brand	AutomationDirect
Item	Audible alarm buzzer
Loudness Decibel	80 dB at 10cm
Tone Frequency	2.4 kHz
Tone Type	Pulse
Touch to Acknowledge	No
Voltage Rating	120 VAC/VDC
Barrel Size	22mm
Mounting	Panel
Housing Material	Plastic
Color	Black
IP Rating	IP65

Agency Approvals

UL Listed File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ECX2070-127.pdf>
See store item page for other formats.