

# ECX2071-127R Cut Sheet



AutomationDirect audible alarm buzzer, 80 dB at 10cm, 2.8 kHz tone frequency, pulse tone(s), 120 VAC/VDC, permanent LED indicator(s), red, 22mm, panel mount, plastic housing, red, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ECX2071-127R>

## Technical Specifications

|                             |                      |
|-----------------------------|----------------------|
| <b>Brand</b>                | AutomationDirect     |
| <b>Item</b>                 | Audible alarm buzzer |
| <b>Loudness Decibel</b>     | 80 dB at 10cm        |
| <b>Tone Frequency</b>       | 2.8 kHz              |
| <b>Tone Type</b>            | Pulse                |
| <b>Touch to Acknowledge</b> | No                   |
| <b>Voltage Rating</b>       | 120 VAC/VDC          |
| <b>Indicator</b>            | Permanent LED        |
| <b>Light Color(s)</b>       | Red                  |
| <b>Barrel Size</b>          | 22mm                 |
| <b>Mounting</b>             | Panel                |
| <b>Housing Material</b>     | Plastic              |
| <b>Color</b>                | Red                  |
| <b>IP Rating</b>            | IP65                 |

## Agency Approvals

|                            |  |
|----------------------------|--|
| <b>UL Listed File #</b>    | None                                   |
| <b>UL Hazardous File #</b> | None                                   |
| <b>CE</b>                  | <a href="#">View CE declarations</a>   |
| <b>RoHS Status</b>         | Yes (See CE Doc)                       |
| <b>EU REACH</b>            | <a href="#">View EU REACH document</a> |
| <b>Other</b>               | None                                   |