

# EHCC2DIU Cut Sheet



Edison modular fuse holder, with indicator, accepts Class CC fuses, 30A, 600V, 2-pole, 18-4 AWG copper only, integral pressure plate with separate spade connection, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EHCC2DIU>

## Technical Specifications

<b>Brand</b>	Edison
<b>Item</b>	Fuse holder
<b>Modular</b>	Yes
<b>Blown Fuse Indicator</b>	Yes
<b>Multi-Wire</b>	No
<b>Accepts Fuse Class</b>	Class CC
<b>Amperage Rating</b>	30A
<b>Voltage Rating</b>	600V

<b>Number of Poles</b>	2
<b>Conductor Size</b>	18-4 AWG copper only
<b>Conductor Connection Type</b>	Integral pressure plate with separate spade connection
<b>SCCR Rating</b>	200kA SCCR
<b>Fuse Connection Type</b>	Clip with reinforced spring
<b>Mounting</b>	35mm DIN rail

## Agency Approvals

<b>UL Listed File #</b>	E300536
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	47235
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/EHCC2DIU.pdf>  
See store item page for other formats.