

# EHCC3DIU-4 Cut Sheet



Edison modular fuse holder, with indicator, accepts Class CC fuses, 30A, 600V, 3-pole, 18-4 AWG copper only, integral pressure plate with separate spade connection, 35mm DIN rail mount. Package of 4.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EHCC3DIU-4>

## Technical Specifications

<b>Brand</b>	Edison
<b>Item</b>	Fuse holder
<b>Modular</b>	Yes
<b>Blown Fuse Indicator</b>	Yes
<b>Multi-Wire</b>	No
<b>Accepts Fuse Class</b>	Class CC
<b>Amperage Rating</b>	30A
<b>Voltage Rating</b>	600V

<b>Number of Poles</b>	3
<b>Conductor Size</b>	18-4 AWG copper only
<b>Conductor Connection Type</b>	Integral pressure plate with separate spade connection
<b>SCCR Rating</b>	200kA SCCR
<b>Fuse Connection Type</b>	Clip with reinforced spring
<b>Mounting</b>	35mm DIN rail
<b>Quantity per Pack</b>	4

## Agency Approvals

<b>UL Listed File #</b>	E300536
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	47235
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None