

EHM1DIU Cut Sheet



Edison modular fuse holder, with indicator, accepts Class Midget fuses, 30A, 600V, 1-pole, 18-4 AWG copper only, integral pressure plate with separate spade connection, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EHM1DIU>

Technical Specifications

Brand	Edison
Item	Fuse holder
Modular	Yes
Blown Fuse Indicator	Yes
Multi-Wire	No
Accepts Fuse Class	Class Midget
Amperage Rating	30A
Voltage Rating	600V
Number of Poles	1
Conductor Size	18-4 AWG copper only
Conductor Connection Type	Integral pressure plate with separate spade connection
SCCR Rating	200kA SCCR
Fuse Connection Type	Clip with reinforced spring
Mounting	35mm DIN rail

Agency Approvals

UL Listed File #	None
UL Recognized File #	E300536
UL Hazardous File #	None
CE	View CE declarations
CSA File #	47235
RoHS Status	No
EU REACH	View EU REACH document
Other	None