

# EHS-M1TE Cut Sheet



Patlite audible signal horn, 110 dB at 1m, 293 Hz to 3.5 kHz tone frequency, (32) selectable tone(s), 12-24 VDC, bracket mount, polycarbonate housing, off-white, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EHS-M1TE>

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	Audible signal horn
<b>Loudness Decibel</b>	110 dB at 1m
<b>Tone Frequency</b>	293 Hz to 3.5 kHz
<b>Tone Type</b>	(32) selectable
<b>Touch to Acknowledge</b>	No
<b>Voltage Rating</b>	12-24 VDC
<b>Mounting</b>	Bracket
<b>Housing Material</b>	Polycarbonate
<b>Color</b>	Off-white
<b>IP Rating</b>	IP65

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	S24210
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	NONE
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>