

EHS-M2TE Cut Sheet



Patlite audible signal horn, 110 dB at 1m, 293 Hz to 3.5 kHz tone frequency, (32) selectable tone(s), 100-240 VAC, bracket mount, polycarbonate housing, off-white, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EHS-M2TE>

Technical Specifications

Brand	Patlite
Item	Audible signal horn
Loudness Decibel	110 dB at 1m
Tone Frequency	293 Hz to 3.5 kHz
Tone Type	(32) selectable
Touch to Acknowledge	No
Voltage Rating	100-240 VAC
Mounting	Bracket
Housing Material	Polycarbonate
Color	Off-white
IP Rating	IP65

Agency Approvals

UL Listed File #	None
UL Recognized File #	S24210
UL Hazardous File #	None
CE	None
CSA File #	NONE
RoHS Status	No
EU REACH	View EU REACH document