

ELT-050-L140 Cut Sheet



AchieVe hydrostatic submersible level transmitter, 0 to 50 psig (115.5ft of water column) sensing range, 4-20 mA, 0.825in diameter housing, shielded and vented 140ft cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ELT-050-L140>

Technical Specifications

Brand	AchieVe
Item	Submersible level transmitter
Sensor Type	Hydrostatic
Sensing Range	0 to 50 psig (115.5ft of water column)
Mounting	Vertical suspension
Process Temperature	-20 to 60 deg C
Output	4-20 mA
Operating Voltage	8-32 VDC
Housing Size	0.825in diameter
Housing Material	Stainless steel
Electrical Connection	Shielded and vented 140ft cable
Jacket Material	Polyethylene

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ELT-050-L140.pdf>
See store item page for other formats.