

EMF33AM23B Cut Sheet



AutomationDirect EMI input filter, 240 VAC, 3-phase, 33A, panel mount, EMI/RFI filtering, drive rated, standard performance, screw terminals and ring terminals. For use with 3-phase GS10, GS20, GS20X and GS30 series AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EMF33AM23B>

Technical Specifications

Brand	AutomationDirect
Item	Input filter
Filter Type	EMI
Filter Voltage Rating	240 VAC
Number of Input Phases	3
Amperage Rating	33A
On/Off Switch	No
Fused	No

Mounting	Panel
Filtering	EMI/RFI
Filter Application	Drive rated
Filter Performance Level	Standard performance
Connector Type	Screw terminals and ring terminals
For Use With	3-phase GS10, GS20, GS20X and GS30 series AC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	E220810
UL Hazardous File #	None
CE	View CE declarations
CSA File #	none
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/EMF33AM23B.pdf>
See store item page for other formats.