

# EN4DSC20228GY Cut Sheet



Hammond Eclipse series disconnect enclosure, NEMA 3R/4/12/13, right flange, 20 x 22 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EN4DSC20228GY>

## Technical Specifications

|                                     |                       |
|-------------------------------------|-----------------------|
| <b>Brand</b>                        | Hammond               |
| <b>Item</b>                         | Disconnect enclosure  |
| <b>Series</b>                       | Eclipse               |
| <b>Slope Top</b>                    | No                    |
| <b>NEMA Rating</b>                  | 3R/4/12/13            |
| <b>IP Rating</b>                    | IP66                  |
| <b>Disconnect Mounting</b>          | Right flange          |
| <b>Nominal Enclosure Dimensions</b> | 20 x 22 x 8in (HxWxD) |
| <b>Enclosure Height</b>             | 20.00in               |
| <b>Enclosure Width</b>              | 22.00in               |
| <b>Enclosure Depth</b>              | 8.84in                |
| <b>Mounting</b>                     | Wall                  |
| <b>Integral Mounting Feet</b>       | No                    |
| <b>Integral Mounting Flange</b>     | No                    |
| <b>Dual Access</b>                  | No                    |

|                                  |   |
|----------------------------------|---|
| <b>Knockouts</b>                 | No  |
| <b>Material</b>                  | Carbon steel  |
| <b>Color</b>                     | ANSI 61 gray  |
| <b>Finish</b>                    | Powder coat   |
| <b>Cover Type</b>                | Single-door   |
| <b>Hinge Type</b>                | Concealed hinges  |
| <b>Number of Hinges Per Door</b> | 2   |
| <b>Latch Type</b>                | 2-point padlocking handle   |
| <b>Padlockable</b>               | Yes   |
| <b>Keylocking</b>                | No  |
| <b>Subpanel</b>                  | Purchase subpanel separately  |
| <b>Additional Information</b>    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR21001                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |