

EN4DSC30268GY Cut Sheet



Hammond Eclipse series disconnect enclosure, NEMA 3R/4/12/13, right flange, 30 x 26 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EN4DSC30268GY>

Technical Specifications

Brand	Hammond
Item	Disconnect enclosure
Series	Eclipse
Slope Top	No
Vented	No
NEMA Rating	3R/4/12/13
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	30 x 26 x 8in (HxWxD)
Enclosure Height	30.00in
Enclosure Width	26.00in
Enclosure Depth	8.84in

Mounting	Wall
Integral Mounting Feet	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	3
Latch Type	2-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Purchase subpanel separately

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/EN4DSC30268GY.pdf>
See store item page for other formats.