

EN4SD202010S16 Cut Sheet



Hammond Eclipse series enclosure, NEMA 3R/4/4X/12/13, 20 x 20 x 10in (HxWxD), wall mount, 316 stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush 316 stainless steel latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EN4SD202010S16>

Technical Specifications

Brand	Hammond
Item	Enclosure
Series	Eclipse
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	20 x 20 x 10in (HxWxD)
Enclosure Height	20.00in
Enclosure Width	20.00in
Enclosure Depth	10.82in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	316 stainless steel
Finish	#4 brush
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Latch Type	1/4-turn semi-flush 316 stainless steel latch
Number Of Latches	1
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document