

EN4SD24248SSWH Cut Sheet



Hammond Eclipse series enclosure, NEMA 3R/4/4X/12/13, 24 x 24 x 8in (HxWxD), wall mount, 304 stainless steel, RAL 9003 white, powder coat finish, single-door, 3-point 316 stainless steel padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EN4SD24248SSWH>

Technical Specifications

Brand	Hammond
Item	Enclosure
Series	Eclipse
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	24 x 24 x 8in (HxWxD)
Enclosure Height	24.00in
Enclosure Width	24.00in
Enclosure Depth	8.84in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	304 stainless steel
Color	RAL 9003 white
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Concealed hinges
Number of Hinges Per Door	2
Latch Type	3-point 316 stainless steel padlocking handle
Number Of Latches	1
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document