

EN4SD603610SSR Cut Sheet



Hammond Eclipse series enclosure, NEMA 3R/4/4X/12/13, 60 x 36 x 10in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush 316 stainless steel latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EN4SD603610SSR>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Hammond |
| Item | Enclosure |
| Series | Eclipse |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 3R/4/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 60 x 36 x 10in (HxWxD) |
| Enclosure Height | 60.00in |
| Enclosure Width | 36.00in |
| Enclosure Depth | 10.82in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|----------------------------------|---|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | 304 stainless steel |
| Finish | #4 brush |
| Cover Type | Single-door |
| Hinge Type | Concealed hinges |
| Number of Hinges Per Door | 4 |
| Latch Type | 1/4-turn semi-flush 316 stainless steel latch |
| Number Of Latches | 5 |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |