

EN4TD24428GY Cut Sheet



Hammond Eclipse series enclosure, NEMA 3R/12, 24 x 42 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, double-door, 3-point keylocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EN4TD24428GY>

Technical Specifications

Brand	Hammond	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Series	Eclipse	Knockouts	No
Subpanel	Purchase subpanel separately	Material	Carbon steel
Slope Top	No	Color	ANSI 61 gray
NEMA Rating	3R/12	Finish	Powder coat
IP Rating	IP54	Cover Type	Double-door
Nominal Enclosure Dimensions	24 x 42 x 8in (HxWxD)	Hinge Type	Concealed hinges
Enclosure Height	24.00in	Number of Hinges Per Door	2
Enclosure Width	42.00in	Latch Type	3-point keylocking handle
Enclosure Depth	8.82in	Number Of Latches	1
Mounting	Wall	Padlockable	No
Integral Mounting Feet	No	Keylocking	Yes

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document