

EPDB306 Cut Sheet



Edison enclosed power distribution block, 380A, 1-pole, line side:
1 opening accepts 500 MCM to 6 AWG, load side: 6 openings
accept 2 AWG to 14 AWG, panel mount, UL 1953 listed.

For complete product information, please see this item on our
store at the following link:



<https://www.automationdirect.com/pn/EPDB306>

Technical Specifications

Brand	Edison
Item	Enclosed Power distribution block
Amperage Rating	380A
Number of Poles	1
Line Side Openings	1 opening accepts 500 MCM to 6 AWG
Load Side Openings	6 openings accept 2 AWG to 14 AWG
Mounting	Panel
SCCR Rating	200kA SCCR
UL Rating	UL 1953 listed
Additional Information	Suitable for branch and feeder circuits

Agency Approvals

UL Listed File #	E256146
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	700490
RoHS Status	No
EU REACH	View EU REACH document
Other	None