

EPDB512 Cut Sheet



Edison enclosed power distribution block, finger-safe, 570A, 1-pole, line side: 2 openings accept 300 MCM to 4 AWG, load side: 12 openings accept 4AWG to 14 AWG, DIN rail mount, UL 1953 listed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EPDB512>

Technical Specifications

Brand	Edison
Item	Power distribution block
Terminal Block Type	Enclosed
Amperage Rating	570A
Number of Poles	1
Line Side Openings	2 openings accept 300 MCM to 4 AWG
Load Side Openings	12 openings accept 4AWG to 14 AWG
Mounting	DIN rail
SCCR Rating	200kA SCCR
UL Rating	UL 1953 listed
IP Rating	IP20
Additional Information	Suitable for branch and feeder circuits

Agency Approvals

UL Listed File #	E256146
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	700490
RoHS Status	No
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/EPDB512.pdf>
See store item page for other formats.