

EPDB702 Cut Sheet



Edison enclosed power distribution block, finger-safe, 760A, 1-pole, line side: 2 openings accept 500 MCM to 6 AWG, load side: 2 openings accept 500 MCM to 6 AWG, panel mount, UL 1953 listed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EPDB702>

Technical Specifications

Brand	Edison
Item	Power distribution block
Terminal Block Type	Enclosed
Amperage Rating	760A
Number of Poles	1
Line Side Openings	2 openings accept 500 MCM to 6 AWG
Load Side Openings	2 openings accept 500 MCM to 6 AWG
Mounting	Panel
SCCR Rating	200kA SCCR
UL Rating	UL 1953 listed
IP Rating	IP20
Additional Information	Suitable for branch and feeder circuits

Agency Approvals

UL Listed File #	E256146
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	700490
RoHS Status	No
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/EPDB702.pdf>
See store item page for other formats.