

EPS25-100WC-1001 Cut Sheet



ProSense digital pressure sensor, -5 to 100.4 inches of water column range, Output: switch (N.O./N.C.), PNP/NPN selectable, Output 2: switch (N.O./N.C.), PNP/NPN selectable or 4-20 mA/0-10 VDC, 1/4in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EPS25-100WC-1001>

Technical Specifications

| | |
|-------------------------------|--|
| Brand | ProSense |
| Item | Digital pressure sensor |
| Pressure Range | -5 to 100.4 inches of water column |
| Output | Switch (N.O./N.C.), PNP/NPN selectable |
| Output 2 | Switch (N.O./N.C.), PNP/NPN selectable or 4-20 mA/0-10 VDC |
| Process Connection | 1/4in male NPT |
| Electrical Connection | 4-pin M12 quick-disconnect |
| Operating Voltage | 18-30 VDC |
| Display Type | 4-digit, two-color LED display |
| Application | For use with compatible liquids or gases |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E320431 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |