

# EPS25-36-1003 Cut Sheet



ProSense digital pressure sensor, 0 to 36.2 psig range, Output: switch (N.O./N.C.), PNP/NPN selectable, Output 2: switch (N.O./N.C.), PNP/NPN selectable, 1/4in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EPS25-36-1003>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Digital pressure sensor
<b>Pressure Range</b>	0 to 36.2 psig
<b>Output</b>	Switch (N.O./N.C.), PNP/NPN selectable
<b>Output 2</b>	Switch (N.O./N.C.), PNP/NPN selectable
<b>Display Type</b>	4-digit, two-color LED display
<b>Operating Voltage</b>	18-30 VDC
<b>Process Connection</b>	1/4in male NPT
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Media Type</b>	Liquid and gases
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E320431
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/EPS25-36-1003.pdf>  
See store item page for other formats.