

EPS25-360-1001 Cut Sheet



ProSense digital pressure sensor, -14.5 to 362.5 psig range, Output: switch (N.O./N.C.), PNP/NPN selectable, Output 2: switch (N.O./N.C.), PNP/NPN selectable or 4-20 mA/0-10 VDC, 1/4in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EPS25-360-1001>

Technical Specifications

Brand	ProSense
Item	Digital pressure sensor
Pressure Range	-14.5 to 362.5 psig
Output	Switch (N.O./N.C.), PNP/NPN selectable
Output 2	Switch (N.O./N.C.), PNP/NPN selectable or 4-20 mA/0-10 VDC
Process Connection	1/4in male NPT
Electrical Connection	4-pin M12 quick-disconnect
Operating Voltage	18-30 VDC
Display Type	4-digit, two-color LED display
Application	For use with compatible liquids or gases
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document