

EPS25-3620-1003 Cut Sheet



ProSense digital pressure sensor, 0 to 3620 psig range, Output: switch (N.O./N.C.), PNP/NPN selectable, Output 2: switch (N.O./N.C.), PNP/NPN selectable, 1/4in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EPS25-3620-1003>

Technical Specifications

Brand	ProSense
Item	Digital pressure sensor
Pressure Range	0 to 3620 psig
Output	Switch (N.O./N.C.), PNP/NPN selectable
Output 2	Switch (N.O./N.C.), PNP/NPN selectable
Process Connection	1/4in male NPT
Electrical Connection	4-pin M12 quick-disconnect
Operating Voltage	18-30 VDC
Display Type	4-digit, two-color LED display
Application	For use with compatible liquids or gases
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document