

# ESS21S12.V Cut Sheet



Schmersal selector switch, IP65, 30mm, 2-position, maintained, key removable left and right position, operator only, plastic base, metal bezel, Operator: black, key-operated, 36mm, round, metal. Requires contact blocks.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ESS21S12.V>

## Technical Specifications

Brand	Schmersal
Item	Selector switch
Barrel Size	30mm
IP Rating	IP65
Number Of Positions	2
Action	Maintained
Key Removable Position	Key removable left and right position
Contact Type	Operator only

Base Material	Plastic
Bezel Material	Metal
Operator Color	Black
Operator Type	Key-operated
Operator Size	36mm
Operator Shape	Round
Operator Material	Metal
Requires	Contact blocks

## Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/ESS21S12.V.pdf>  
See store item page for other formats.