

# ESS32S123.V Cut Sheet



Schmersal selector switch, IP65, 30mm, 3-position, maintained, key removable left, right and center position, operator only, plastic base, metal bezel, Operator: black, key-operated, 36mm, round, metal. Requires contact blocks.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ESS32S123.V>

## Technical Specifications

Brand	Schmersal
Item	Selector switch
Barrel Size	30mm
IP Rating	IP65
Number Of Positions	3
Action	Maintained
Key Removable Position	Key removable left, right and center position
Contact Type	Operator only
Base Material	Plastic
Bezel Material	Metal
Operator Color	Black
Operator Type	Key-operated
Operator Size	36mm
Operator Shape	Round
Operator Material	Metal
Requires	Contact blocks

## Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>