

ESS32S3.V Cut Sheet



Schmersal selector switch, IP65, 30mm, 3-position, maintained, key removable right position, operator only, plastic base, metal bezel, Operator: black, key-operated, 36mm, round, metal. Requires contact blocks.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ESS32S3.V>

Technical Specifications

| | |
|-------------------------------|------------------------------|
| Brand | Schmersal |
| Item | Selector switch |
| Barrel Size | 30mm |
| IP Rating | IP65 |
| Number Of Positions | 3 |
| Action | Maintained |
| Key Removable Position | Key removable right position |
| Contact Type | Operator only |
| Base Material | Plastic |
| Bezel Material | Metal |
| Operator Color | Black |
| Operator Type | Key-operated |
| Operator Size | 36mm |
| Operator Shape | Round |
| Operator Material | Metal |
| Requires | Contact blocks |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E57648 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |