

ESW-B9D15A-R24 Cut Sheet



WEG Electric ESW series manual motor starter, pushbutton, 9A, 3-pole, 120 VAC (50/60Hz) coil voltage, thermal overload, 1.2-1.8A adjustable, NEMA 1.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ESW-B9D15A-R24>

Technical Specifications

| | |
|---------------------------------|---------------------|
| Brand | WEG Electric |
| Series | ESW |
| Item | Motor starter |
| Starter Type | Manual |
| Actuator Type | Pushbutton |
| Coil Voltage | 120 VAC (50/60Hz) |
| Amperage Rating | 9A |
| Voltage Rating | 600 VAC |
| Horsepower Rating | 3/4hp |
| Relay Type | Thermal overload |
| Operation Type | Bi-metallic |
| Full Load Amperage Range | 1.2-1.8A adjustable |

| | |
|--------------------------------|-----------------------------------|
| Number of Poles | 3 |
| Power Poles | (3) N.O. |
| Auxiliary Contacts | (1) N.O./ (1) N.C. |
| Trip Class | Trip Class 10 |
| Phase Loss Sensitive | Yes |
| Ground Fault Protection | No |
| SCCR Rating | 5kA SCCR |
| UL Rating | UL 508 rated |
| Enclosure Type | NEMA 1 |
| Mounting | Wall |
| Connection | Screw terminal |
| Includes | Start, stop and reset pushbuttons |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E202315 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ESW-B9D15A-R24.pdf>
See store item page for other formats.