

ESW-B9D39A-R23 Cut Sheet



WEG Electric ESW series manual motor starter, pushbutton, 9A, 3-pole, 480 VAC (50/60Hz) coil voltage, thermal overload, 0.8-1.2A adjustable, NEMA 1.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ESW-B9D39A-R23>

Technical Specifications

Brand	WEG Electric
Series	ESW
Item	Motor starter
Starter Type	Manual
Actuator Type	Pushbutton
Coil Voltage	480 VAC (50/60Hz)
Amperage Rating	9A
Voltage Rating	600 VAC
Horsepower Rating	1/2hp
Relay Type	Thermal overload
Operation Type	Bi-metallic
Full Load Amperage Range	0.8-1.2A adjustable

Number of Poles	3
Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O./ (1) N.C.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
SCCR Rating	5kA SCCR
UL Rating	UL 508 rated
Enclosure Type	NEMA 1
Mounting	Wall
Connection	Screw terminal
Includes	Start, stop and reset pushbuttons

Agency Approvals

UL Listed File #	E202315
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ESW-B9D39A-R23.pdf>
See store item page for other formats.