

ESWE-B18D39KX-D11 Cut Sheet



WEG Electric ESWE series combination Type-E motor starter, 18A, 3-pole, 480 VAC (50/60Hz) coil voltage, bi-metallic, 10.0–16.0A adjustable, 208A instantaneous trip rating, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ESWE-B18D39KX-D11>

Technical Specifications

Brand	WEG Electric
Series	ESWE
Item	Motor starter
Starter Type	Combination Type-E
Coil Voltage	480 VAC (50/60Hz)
Amperage Rating	18A
Voltage Rating	600 VAC
Horsepower Rating	10 hp
Overload Type	Bi-metallic
Full Load Amperage Range	10.0–16.0A adjustable
Instantaneous Trip Rating	208A
Number of Poles	3

Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O./ (1) N.C.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
SCCR Rating	25 kA SCCR
UL Rating	UL 508A rated
Enclosure Type	NEMA 4/4X
Mounting	Wall
Connection	Screw terminal
Includes	Rotary disconnect switch, HOA selector switch, start/stop pushbuttons, and run indication lights

Agency Approvals

UL Listed File #	E215390
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ESWE-B18D39KX-D11.pdf>
See store item page for other formats.