

ESWE-B9V24KX-D06 Cut Sheet



WEG Electric ESWE series combination Type-E motor starter, 9A, 3-pole, 208-240 VAC (60Hz)/180-208 VAC (50Hz) coil voltage, bi-metallic, 1.0-1.6A adjustable, 21A instantaneous trip rating, NEMA 4/4X.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ESWE-B9V24KX-D06>

Technical Specifications

Brand	WEG Electric
Series	ESWE
Item	Motor starter
Starter Type	Combination Type-E
Coil Voltage	208-240 VAC (60Hz)/180-208 VAC (50Hz)
Amperage Rating	9A
Voltage Rating	600 VAC
Horsepower Rating	3/4 hp
Overload Type	Bi-metallic
Full Load Amperage Range	1.0-1.6A adjustable
Instantaneous Trip Rating	21A
Number of Poles	3

Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O./(1) N.C.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
SCCR Rating	25 kA SCCR
UL Rating	UL 508A rated
Enclosure Type	NEMA 4/4X
Mounting	Wall
Connection	Screw terminal
Includes	Rotary disconnect switch, HOA selector switch, start/stop pushbuttons, and run indication lights

Agency Approvals

UL Listed File #	E215390
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/ESWE-B9V24KX-D06.pdf>
See store item page for other formats.