

ESWS-B25V24A-RM33 Cut Sheet



WEG Electric ESWS series manual motor starter, pushbutton, 25A, 2-pole, 208-240 VAC (60Hz)/180-208 VAC (50Hz) coil voltage, thermal overload, 15.0-23.0.A Adjustable, NEMA 1.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ESWS-B25V24A-RM33>

Technical Specifications

Brand	WEG Electric
Series	ESWS
Item	Motor starter
Starter Type	Manual
Actuator Type	Pushbutton
Coil Voltage	208-240 VAC (60Hz)/180-208 VAC (50Hz)
Amperage Rating	25A
Voltage Rating	600 VAC
Horsepower Rating	3hp
Relay Type	Thermal overload
Operation Type	Bi-metallic
Full Load Amperage Range	15.0-23.0.A Adjustable
Number of Poles	2
Power Poles	(2) N.O.
Auxiliary Contacts	(1) N.O./ (1) N.C.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
SCCR Rating	5kA SCCR
UL Rating	UL 508 rated
Enclosure Type	NEMA 1
Mounting	Wall
Connection	Screw terminal
Includes	Start, stop and reset pushbuttons

Agency Approvals

UL Listed File #	E202315
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document