

# EVC179 Cut Sheet



AutomationDirect connection cable, M12 right-angle female to pigtail, 4-pole, 10-36 VDC, PNP LED, PUR jacket, black, 16.4ft/5m cable length, IP67, IP68 and IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EVC179>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Cable
<b>Cable Type</b>	Connection
<b>Connection 1</b>	M12 right-angle female
<b>Connection 2</b>	Pigtail
<b>Number of Poles</b>	4
<b>Voltage Rating</b>	10-36 VDC
<b>Indicator</b>	PNP LED
<b>Jacket Material</b>	PUR
<b>Jacket Color</b>	Black
<b>Cable Length</b>	16.4ft/5m
<b>IP Rating</b>	IP67, IP68 and IP69K

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E191684
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>