

EVC324 Cut Sheet



AutomationDirect connection cable, M12 right-angle female to axial male, 4-pole, 10-36 VDC, PNP LED, PUR jacket, black, 3.2ft/1m cable length, IP67, IP68 and IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/EVC324>

Technical Specifications

| | |
|-----------------|------------------------|
| Brand | AutomationDirect |
| Item | Cable |
| Cable Type | Connection |
| Connection 1 | M12 right-angle female |
| Connection 2 | Axial male |
| Number of Poles | 4 |
| Voltage Rating | 10-36 VDC |
| Indicator | PNP LED |
| Jacket Material | PUR |
| Jacket Color | Black |
| Cable Length | 3.2ft/1m |
| IP Rating | IP67, IP68 and IP69K |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E191684 |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |
| Other | None |